

755 nm Laser

Powerful absorption, combined with continuous cooling, Treatment coverage, comfort, and low maintenance, Enables the treatment of a wide range of hair types and colors, Especially light-colored and thin hair.

808 nm Diode Laser

Complete more treatment sessions in less time with this large spot size applicator. Treat larger areas faster, while offering patients a safe and highly effective hair removal procedure.

1064 nm ND-Yag Laser

The YAG 1064 uses a diode laser based on an Nd: YAG wavelength, allowing for moderate energy absorption by the melanin chromosphere, and is optimally suited for patients with darker skin tones.



808nm/755nm/1064nm

TECHNICAL SPECIFICATION

MODEL NAME	WAVELENGTH PRO-X	WAVELENGTH PRO-K	WAVELENGTH PRO-V
LASER COOLING TEMPERATURE	Sapphire Cooling	Sapphire Cooling	Sapphire Cooling
OUTPUT POWER	1200W/ 600W optional	1200W/ 600W optional	1200W/ 600W optional
ENERGY DENSITY	2-120j/cm²	1 - 100 J/cm²	2-120j/cm²
WORKING TEMPERATURE	_	+15°C+30°C	_
STORAGE TEMPERATURE	_	-20°C∼+55°C	_
WAVELENGTH	808nm/755nm/ 1064nm	808nm/755nm/ 1064nm	808nm/755nm/ 1064nm
POWER SUPPLY	_	AC230V, 50Hz AC110V, 60Hz	_
PULSE WIDTH	_	100ms, 200ms, 400ms or Auto	<u> </u>
SPOT SIZE	12*12mm	12*12mm	12*12mm
SCREEN	(15" Touch Screen)	(15" Touch Screen)	(15" Touch Screen)
FREQUENCY		Slow(1-4Hz)	
		Mode(5-9Hz)	
		Fast(10-20Hz)	

Code Aesthetics

B2-34/A First Floor Yamuna Vihar, Delhi-110053 Contact: +91 9716830460 Email: info@codeesthetics.com www.codeesthetics.com







SERIES



INTRODUCTION

A breakthrough hair removal platform that combines ultimate functionality with unparalleled comfort. Thanks to its adequate 12x12mm² spot size and advanced cooling system, treatments are now much faster and pain free – offering a significantly improved solution for patients and practitioners a like. Leverages the benefits of 3 combined wavelengths, with an improved patient experience and a business-oriented approach, creating a unique and result driven new solution in the world of professional hair removal.

CONTINUOUS CONTACT COOLING

3C is an advanced technology that continuously cools skin and facilitates range-controlled temperature throughout the entire treatment. The 3C cold sapphire tip minimizes epidermal risks while maintaining heat with in the dermis where hair follicles are treated. Temperature remains controlled and constant which contributes to the diode's efficiency.

- ★ Combination 3 wavelength. apply on six skin types
- ★ Best laser for painless and permanent jair removal non- inasive
- ★ The tip handpeice cool down to 0-30c makes treatment confortable and effective

WAVELENGTH PRO-V



3 WAVE TECHNOLOGY

Featuring its exclusive 3 wave technology, wavelength pro-x combines the three most effective laser wavelengths into a single applicator, simultaneously targeting different tissue depths and anatomical structures within the hair follicle. By combining the absorption and penetration levels of different wavelengths, along with extended treatment coverage, increased comfort and low maintenance requirements, wavelength pro-x is the safest and most efficient hair removal treatment available today. 3 Dimension technology for one superior hair removal solution.

8' TFT TOUCH SCREEN

FRIENDLY AND FUNCTIONAL

Equipped with a new large sized 8' TFT touch screen, with preset parameters, practitioners can enjoy a more intuitive, user friendly work experience.

EXCEPTIONALLY ADEQUATE SPOT SIZE

Wavelenth Pro-X features 3 wave 12x12mm2 A unique and efficient new applicator with An special spot size of 12x12mm2, Capable of working on a grid of 600cm square. This breakthrough applicator makes treatments Much faster and pain free, significantly cutting Treatment times and ensuring a more comfortable Experience for patients.

- ★ 20 million shots lifespan maximizes your return of investment
- ★ 52kg lightest hair removal machine
- ★ 3 multi-wavelength reach diffrent skin layer & make all the hair folicile absorb the energy evenly



THEORY

It uses special laser with 3 wavelengths-808nm/755nm/1064nm that can penetrate to hair follicle. Using selective light absorption theory, laser can be preferentially absorbed by the melanin of the hair and then heating the hair shaft and hair follicle, moreover to destroy the hair follicle and oxygen organization around hair follicle.

For the widest range of hair types and colors wavelenth pro-k offers breakhrough hair removal technology ising a diode laser based on an 808 wavelwnth the powerful absorption-that is possible with the 808 wavelenth cmbined with the contact cooling treatment coverage comfort and low maintanance of the diode laser provides on ideal solution for the widest range of hair types and color

WAVELENGTH PRO-K - SPEED

Half the treatment time with 20Hz repetition perform more treatment sessions in less time with hight energy density spot size applicator allowing you to quickly treat larger areas. while offering your patient the fatest and most effective hair removal possible.

Compact Handpiece

- 1. versatile treatment methods
- 2. an ergonomic and innovation lightweight wavelength Beauty handpeice design
- 3. make patient more comfortable and practitioners more enjoyable.